

Safety Data Sheet

According to Hazard Communication Standard (29 CFR 1910.1200)

R-134a

Issue date: 04/29/2015 Version 1.0 **Revision date: 11/20/2018**

1. Identification

Product name R-134a

Synonyms

CAS# See section 3

Product code

Product use Used as refrigerants.

Manufacturer/Supplier

Supplier (Manufacturer): iGas USA, Inc.

Address: 8105 Anderson Road, Tampa, FL 33634

acoughlin@bmp-usa.com Contact person (E-mail):

Telephone: (813) 443-0757 (813) 886-7900 Fax:

Emergency telephone Number: Chemtrec: 1-800-424-9300

2. Hazard(s) identification

GHS classification

Physical hazards Gases under pressure Liquefied gas

Health hazards Not classified **Environmental hazards** Not classified

GHS label elements

Hazard Pictograms



Signal word Warning

Hazard statement Contains gas under pressure; may explode if heated.

Precautionary statement

Prevention Not applicable. Response Not applicable.

Protect from sunlight. Store in a well-ventilated place. **Storage**

Not applicable. **Disposal**

3. Composition / information on ingredients

Components	CAS#	Percent
Norflurane	811-97-2	≥99.9%

4. First-aid Measures

First aid procedures

Immediately flush with plenty of water. After initial flushing, remove any contact lenses Eve contact

1/6

SDS US Material name: R-134a Issue date:04-29-2015.

and continue flushing for at least 15 minutes. Have eyes examined and treated by medical personnel.

Thaw affected area with water. Remove contaminated clothing. Caution: clothing may adhere to the skin in case of freeze burns. After contact with skin, wash immediately with plenty of warm water. If symptoms (irritation or blistering) develop, get medical

attention.

Remove victim to fresh air. Keep warm and at rest. If not breathing, give artificial respiration, preferably mouth-to-mouth. If breathing is labored, give oxygen. In the

event of a cardiac arrest, apply external cardiac massage.

Ingestion is unlikely because of the physical properties and is not expected to be hazardous. Do not induce vomiting unless instructed to do so by a physician.

Treat symptoms.

Notes to physician

Ingestion

Skin contact

Inhalation

5. Fire-fighting measures

Flammable properties Not available.

Extinguishing media

Suitable extinguishing media
Use appropriate extinguishing media.
Unsuitable extinguishing media
Not available.

Firefighting equipment/instructions

Shut off gas supply if this can be done safely. If possible, take container out of dangerous zone. Cool cylinders with water spray. Self-contained breathing apparatus (SCBA) may be required if cylinders rupture or release under fire conditions. Carbon oxides, Hydrogen fluoride.

Hazardous combustion products

6. Accidental release measures

Personal precautionsImmediately contact emergency personnel. Keep unnecessary personnel away. Use suitable protective equipment (section 8). Shut off gas supply if this can be done safely.

Isolate area until gas has dispersed.

Environmental precautions Prevent further leakage or spillage if safe to do so. Do not let product enter drains.

Discharge into the environment must be avoided.

Methods for cleaning up

For large releases: Use recommended personal protection and evacuate unprotected

personnel. Shut off the leak if without risk. Ventilate the spill area. If possible, dike and contain spillage. Prevent liquid from entering sewers, sumps or pit areas since vapor can create a suffocating atmosphere. Capture material for recycle or destruction if

suitable equipment is available.

7. Handling and storage

Handling

Avoid causing and inhaling high concentrations of vapor. Atmospheric levels should be controlled to below the occupational exposure limit and kept as low as practicable. Do not put mixture of HFC134a with air or oxygen under pressure. Do not use such

mixtures for leak or pressure testing. Avoid HFC134a contact with flame or very hot

surfaces.

Storage Keep at temperature not exceeding 120 °F (49 °C). Keep in a cool, well ventilated

place. Keep containers dry. Keep away from direct sunlight, heat and sources of

ignition.

8. Exposure controls / personal protection

Control parameters:

OCCUPATIONAL EXPOSURE LIMITS (OEL)

INGREDIENT DATA:

Not Available

EMERGENCY LIMITS:

Ingredient	Original IDLH	Revised IDLH	
Norflurane	Not Available	Not Available	

Exposure controls:

Appropriate engineering controls: Use adequate general or local exhaust ventilation to keep airborne concentrations below the

permissible exposure limits.

Individual protection measures, such as personal protective equipment:

Chemical tight goggles; full face shield in addition if splashing is possible. Eye / face protection

Skin protection Body protection: Impervious gloves if any possibility of skin contact with liquid. Additional

protection may be required such as apron, arm covers, or full body suit, depending upon

conditions.

Hand protection: Wear leather gloves to prevent frostbite injuries from rapidly expanding gas

when handling pressurized gas bottles.

Respiratory protection Not normally needed if controls are adequate. If needed, use MSHA-NIOSH approved

respirator for organic vapors. For high concentrations and oxygen-deficient atmospheres, use

positive pressure air-supplied respirator.

General hygiene

considerations

Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Keep away from

foodstuffs, beverages and feed. Immediately remove all soiled and contaminated clothing.

9. Physical and chemical properties

Appearance

Physical state Gas

Form Compressed liquefied gas

Color Clear, colorless Faint ethereal odor Odor

Odor threshold Not available Not available pН 5.74 Bar (20 °C) Vapor pressure

Melting point/Freezing point -101°C

initial boiling point and boiling range -26.2°C Flash point Not available Not available **Evaporation rate**

Material name: R-134a

Flammability (solid, gas)

Issue date: 04-29-2015. 3/6 Version #:1.0 Revision date: 11-20-2018.

Non-flammable

SDS US

Explosion limits Not available Vapor density Not available Relative density Not available Slightly in water. Solubility (water)

Partition coefficient 1.06 (25 °C) **Auto-ignition temperature** > 743 °C

Decomposition temperature Not available

Specific gravity 1.23 at 20°C (70°F)

Density Not available Flammability limits in air, upper, %by volume Not available

Flammability limits in air, lower, % by volume Not available

VOC Not available Not available Percent volatile

Other data

Viscosity Not available

10. Stability and reactivity

Chemical stability Material is stable under normal conditions.

Conditions to avoid Incompatible materials.

Incompatible materials Finely divided metals, magnesium and alloys containing more than 2% magnesium.

Can react violently if in contact with alkali metals and alkaline earth metals - sodium

potassium and barium.

Hazardous decomposition products Carbon oxides, Hydrogen fluoride.

Possibility of hazardous reactions Can react violently if in contact with alkali or alkali earth metals such as sodium,

potassium or barium. Dangerous on contact with acid or acid fumes, they emit highly

toxic fumes.

11. Toxicological information

Toxicokinetics, metabolism and distribution:

Non-human toxicological data: Not available

Information on toxicological effects:

Acute toxicity:

LD50(Oral, Rat): Not available Not available LD50(Dermal, Rabbit): 1500 mg/m₃/4h LC50(Inhalation, Rat): Skin corrosion/Irritation: Not classified. Serious eye damage/irritation: Not classified Not classified Respiratory or skin sensitization: Not classified Germ cell mutagenicity: Carcinogenicity: Not classified Not classified Reproductive toxicity: Not classified **STOT- single exposure:** Not classified **STOT-repeated exposure: Aspiration hazard:** Not classified

Material name: R-134a

Version #:1.0 Revision date: 11-20-2018. Issue date: 04-29-2015.

SDS US

12. Ecological information

Toxicity:

Acute tox	xicity	Time	Species	Method	Evaluation	Remarks
LC50	450 mg/L	96h	Fish	OECD 203	N/A	N/A
EC50	980 mg/L	48h	Daphnia	OECD 202	N/A	N/A
EC50	N/A	72h	Algae	OECD 201	N/A	N/A

Persistence and degradability: Negligible biodegradation after 28 days.

Bio-accumulative potential: R-134a will not bioconcentrate in fish and aquatic organisms.

Mobility in soil: R-134a will display moderate to high mobility in soil.

Results of PBT & vPvB

assessment:

The substance is not PBT / vPvB.

Other adverse effects: No known significant effects or critical hazards.

13. Disposal considerations

Disposal instructions Dispose of contents/container in accordance with local/regional/national/international

regulations

Contaminated packaging Since emptied containers may retain product residue, follow label warnings even after

container is emptied.

14. Transport information

DOT

Basic shipping requirements:

UN number UN3159

Proper shipping name 1,1,1,2-TETRAFLUOROETHANE (REFRIGERANT GAS R 134a)

Hazard class Packing 2.2 group Environmental -

hazards No

IATA

UN number UN3159

UN proper shipping name 1,1,1,2-TETRAFLUOROETHANE (REFRIGERANT GAS R 134a)

Transport hazard class(es) 2.2
Packing group Environmental hazards No

IMDG

UN number UN3159

UN proper shipping name 1,1,1,2-TETRAFLUOROETHANE (REFRIGERANT GAS R 134a)

Transport hazard class(es) 2.2
Packing group -

Environmental hazards No

15. Regulatory information

Safety, health and environmental regulations/legislation specific for the substance or mixture:

Norflurane (811-97-2) is found on the	"US - Washington Toxic air pollutants and their ASIL, SQER and de minimis	
following regulatory lists	emission values" List.	
	"US Toxic Substances Control Act (TSCA) - Chemical Substance Inventory" List.	

16. Other information, including date of preparation or last revision

Health: 1 **HMIS®ratings**

Flammability: 1

Physical hazard: 3

Health:1 **NFPA** ratings

> Flammability: 1 Instability: 3

The information in the sheet was written based on the best knowledge and experience Disclaimer

currently available.

Issue date 04-29-2015

Material name: R-134a SDS US Version #:1.0 Revision date: 11-20-2018. 6/6