


Safety Data Sheets (SDSs)

For
Global Industrial
2505 Mill Center Parkway, Buford, Georgia, 30518
+1 516 608 3000

Report No: SA2004052S 02001
Preparation Date: April 09, 2020
Total number of pages: 10
Revision Date: N/A
Reviewed by: Vincent Liu
Approved by: Bruce Yu
Testing laboratory: Dongguan Anci Electronic Technology Co.,*Ltd.
1-2 Floor, Building A, No.11, Headquarters 2 Road,
Testing Address: Songshan Lake Hi-tech Industrial, Development Zone,
Dongguan City, Guangdong Pr. China
Applicant's name: Global Industrial
Address: 2505 Mill Center Parkway, Buford, Georgia, 30518
Product name: Lead Acid Battery
Model /Type reference: 6-EVF-100A
Trademark 
Product Specification 12V 100AH
Version Number V1.0



1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

Product Identifier

Product name: Lead Acid Battery

Other means of identification

Product description Model: 6-EVF-100A

Trade mark:



Product Specification 12V 100AH

Recommended use of the chemical and restrictions on use

Recommended Use Used in not portabl electronic equipments

Uses advised against:

- a) Do not dismantle, open or shred secondary cells or batteries.
- b) Do not expose cells or batteries to heat or fire. Avoid storage in direct sunlight.
- c) Do not short-circuit a cell or a battery. Do not store cells or batteries haphazardly in a box or drawer where they may short-circuit each other or be short-circuited by other metal objects.
- d) Do not remove a cell or battery from its original packaging until required for use.
- e) Do not subject cells or batteries to mechanical shock.
- f) In the event of a cell leaking, do not allow the liquid to come in contact with the skin or eyes. If contact has been made, wash the affected area with copious amounts of water and seek medical advice.
- g) Do not use any charger other than that specifically provided for use with the equipment.
- h) Observe the plus (+) and minus (-) marks on the cell, battery and equipment and ensure correct use.
- i) Do not use any cell or battery which is not designed for use with the equipment.
- j) Do not mix cells of different manufacture, capacity, size or type within a device.
- k) Battery usage by children should be supervised.
- l) Seek medical advice immediately if a cell or a battery has been swallowed.
- m) Always purchase the battery recommended by the device manufacturer for the equipment.
- n) Keep cells and batteries clean and dry.
- o) Wipe the cell or battery terminals with a clean dry cloth if they become dirty.
- p) Secondary cells and batteries need to be charged before use. Always

use the correct charger and refer to the manufacturer's instructions or equipment manual for proper charging instructions.

- q) Do not leave a battery on prolonged charge when not in use.
- r) After extended periods of storage, it may be necessary to charge and discharge the cells or batteries several times to obtain maximum performance.
- s) Retain the original product literature for future reference.
 - t) Use only the cell or battery in the application for which it was intended.
- u) When possible, remove the battery from the equipment when not in use.
- v) Dispose of properly.

Details of the supplier and Manufacturer of the safety data sheet:

Applicant	Global Industrial
Applicant Address	2505 Mill Center Parkway, Buford, Georgia, 30518
Company Emergency Phone Number:	+1 516 608 3000
E-mail address:	www.globalindustrial.com
Manufacturer	Global Industrial
Manufacturer Address	2505 Mill Center Parkway, Buford, Georgia, 30518
Telephone number of the supplier:	+1 516 608 3000
E-mail address:	www.globalindustrial.com

2. HAZARDS IDENTIFICATION

Hazards Identification:

The battery is valve regulated type. It is NOT restricted to IATA DGR according to special provision A67 and is NOT restricted to IMDG CODE according to special provision 238.

Emergency Overview:

The internal battery materials may cause severe irritation to eyes and skin. Causes burns.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical characterization: Mixtures

Description:

Product: Consisting of the following components.

Common Chemical Name	Concentration (%)	CAS Number
Lead	60-80	7439-92-1
Diluted Sulfuric Acid	5-20	7664-93-9
Acrylonitrile/Butadiene/Styrene Resin(ABS)	5-10	9003-56-9
AGM Fiberglass Separator	1-5	65997-17-3
Epoxy Resin	0.1-1	--

Note: CAS number is Chemical Abstract Service Registry Number.

4. FIRST-AID MEASURES

First aid measures

First aid is upon rupture of sealed battery.

Eye Contact	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Keep eye wide open while rinsing. Do not rub affected area. Remove contact lenses, if present and easy to do. Continue rinsing. Seek immediate medical attention/advice.
Skin Contact	Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Immediate medical attention is required. May cause an allergic skin reaction.
Inhalation	Remove to fresh air. If breathing has stopped, give artificial respiration. Get medical attention immediately. Do not use mouth-to-mouth method if

	victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. If breathing is difficult, (trained personnel should) give oxygen. Delayed pulmonary edema may occur. Get medical attention immediately if symptoms occur.
Ingestion	Do NOT induce vomiting. Rinse mouth immediately and drink plenty of water. Never give anything by mouth to an unconscious person. Call a physician or poison control center immediately.
Self-protection of the first aider	Avoid contact with skin, eyes or clothing. Use personal protective equipment as required. Wear personal protective clothing (see section 8).

Most important symptoms and effects, both acute and delayed

Itching. Coughing and/ or wheezing. Burning sensation.

Indication of any immediate medical attention and special treatment needed

Notes to Physician	Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated. Do not give chemical antidotes. Asphyxia from glottal edema may occur. Marked decrease in blood pressure may occur with moist rales, frothy sputum, and high pulse pressure. May cause sensitization of susceptible persons. Treat symptomatically.
--------------------	--

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Dry chemical, Sandy soil, Carbon dioxide or appropriate foam.

Specific Hazards Arising from the Chemical

Under fire conditions, batteries may burst and release hazardous decomposition products when exposed to a fire situation.

Formation of toxic gases is possible during heating or in case of fire. In

case of fire, the following can be released:

Carbon monoxide(CO)

Carbon dioxide

Other irritating and toxic gases.

Protective Equipment and Precautions for Firefighters

Firefighters must wear fire resistant protective equipment and appropriate breathing apparatus. The staff must equip with filtermask (full mask) or isolated breathing apparatus. The staff must wear the clothes which can defense the fire and the toxic gas. Put out the fire in the upwind direction. Remove

the container to the open space as soon as possible. Spray water on the containers in the fireplace to keep them cool until finish extinguishment.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal Precautions	Attention!Corrosive material. Avoid contact with skin, eyes or clothing. Ensure adequate ventilation. Use personal protective equipment as required. Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak.
Other information	Refer to protective measures listed in Sections 7 and 8.

Environmental precautions

Refer to protective measures listed in Sections 7 and 8. Prevent further leakage or spillage if safe to do so. Should not be released into the environment. Do not allow to enter into soil/subsoil. Prevent product from entering drains.

Methods and material for containment and cleaning up

Methods for Containment	prevent further leakage or spillage if safe to do so.
Methods for Cleaning up	Use personal protective equipment. Dam up. Cover liquid spill with sand, earth or other Non combustible absorbent material. Pick up and transfer to properly labeled containers. Clean contaminated surface thoroughly.

7. HANDLING AND STORAGE

Precautions for safe handling

Handling	Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes and clothing. Wear personal protective equipment. Wash thoroughly after handling. Use this material with adequate ventilation. The product is not explosive.
----------	---

Conditions for safe storage, including any incompatibilities

Do not storage Battery haphazardly in a box or drawer where they may short-circuit each other or be short-circuited by other metal objects.

Keep out of reach of children.

Do not expose Lithium-ion Polymer Battery to heat or fire. Avoid storage in direct sunlight. Do not store together with oxidizing and acidic materials.

Keep ignition sources away- Do not smoke.

Store in cool, dry and well-ventilated place.

Incompatible Products None known.

8. EXPOSURE CONTROLS AND PERSONAL PROTECTION

(a) Engineering Controls

Use local exhaust ventilation or other engineering controls to control sources of dust, mist, fumes and vapor. Keepaway from heat and open flame. Store in a cool, dry place.

(b) Personal Protective Equipment

Respiratory Protection: Not necessary under normal conditions. **Skin and body Protection:** Not necessary under normal conditions, Wear neoprene or nitrile rubber gloves if handling an open or leaking battery.

Hand protection: Wear neoprene or natural rubber material gloves if handling an open or leaking battery.

Eye Protection: Not necessary under normal conditions, wear safety glasses if handling an open or leaking battery.

(c) Other Protective Equipment

Have a safety shower and eye wash fountain readily available in the immediate work area.

(d) Hygiene Measures

Do not eat, drink, or smoke in work area. Maintain good housekeeping.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical State	Form: Prismatic
	Color: --
	Odour: Odourless
	Odor Threshold: No information available
Change in condition:	
pH, with indication of the concentration	Not determined.
Melting point/freezing point	Not determined.
Initial boiling point and Boiling range:	Not determined.
Flash Point	Not determined.
Evaporation rate	Not determined.
Flammability (solid, gas)	Not determined.
Upper/lower flammability or explosive limits	Not determined.

Vapor Pressure:	Not determined.
Vapor Density:	Not determined.
relative density:	Not determined.
Solubility in Water:	Not determined.
Solubility in other solvents	Not determined.
n-octanol/water partition coefficient	Not determined.
Auto-ignition temperature	Not determined.
Decomposition temperature	Not determined.
Odour threshold	Not determined.
Evaporation rate	Not determined.
Viscosity	Not determined.
Other Information	No further relevant information available.

10. STABILITY AND REACTIVITY

Reactivity: Stable under recommended storage and handling conditions (see section 7, Handling and storage).

Chemical stability: Stable under normal conditions of use, storage and transport.

Thermal decomposition/conditions to be avoided: No decomposition if used according to specifications.

Possibility of Hazardous Reactions: None under normal processing.

Hazardous Polymerization: Hazardous polymerization does not occur.

Conditions to avoid: Strong heating, fire, Incompatible materials.

Incompatible materials: Strong oxidizing agents. Strong acids. Base metals.

Hazardous Decomposition Products: Carbon oxides, Other irritating and toxic gases.

11. TOXICOLOGICAL INFORMATION

Acute toxicity: No data available.

LD/LC50 values relevant for classification:

Not available.

Skin corrosion/irritation: No irritant effect.

Serious eye damage/irritation: Cause serious eye irritation.

Respiratory or skin sensitization: No sensitizing effects known.

Specific target organ system toxicity: No information available.

CMR effects(carcinogenicity, mutagenicity and toxicity for reproduction): No information available.

12. Ecological Information

Toxicity:

Acquatic toxicity:

No further relevant information available.

Persistence and degradability: No further relevant information available.

Bioaccumulative potential: No further relevant information available.

Mobility in soil: No further relevant information available.

Results of PBT and vPvB assessment

PBT: Not applicable.

vPvB: Not applicable.

Other adverse effects: No information available.

13 DISPOSAL CONSIDERATIONS

Waste treatment methods

Recommendation: Must not be disposed together with household garbage.

Do not allow product to reach sewage system

Uncleaned packaging:

Recommendation: Disposal must be made according to official regulations.

14. TRANSPORT INFORMATION

The battery has passed the vibration test, pressure differential test and leakage test at 55°C according to Recommendations on the IMOIMDG CODE. This substance is NOT subject to IMO IMDG CODE according to Special Provision 238.

IATA: Proper Shipping Name: --

UN Number: --

Hazard Class: --

IMO: Proper Shipping Name: --

UN Number: --

Hazard Class: --

Packing Group:--

15. REGULATORY INFORMATION

EU Additional Classification:

S 36/37

Safety Statements: Wear suitable protective clothing and gloves.

16. OTHER INFORMATION

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

Preparation and revision information		
Date of previous revision	Date of this revision	Revision summary
Not applicable	/	The first New SDS

Photo



*****End of SDS*****