SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Material name : ZEP HIGH-TRAFFIC CARPET SPOT REMOVER & CLEANER

Material number : ZUHTC128

Manufacturer or supplier's details

Company : Zep Inc.

Address : 350 Joe Frank Harris Parkway, SE
Emerson, GA 30137

Telephone : 404-352-1680

Emergency telephone numbers		
For SDS Information	:	Compliance Services 1-877-428-9937
For a Medical Emergency	:	877-541-2016 Toll Free - All Calls Recorded
For a Transportation Emergency	:	CHEMTREC: 800-424-9300 - All Calls Recorded. In the District of Columbia 202-483-7616

Recommended use of the chemical and restrictions on use

Note: This product is labeled as a consumer product in accordance with the United States Consumer Product Safety Commission regulations. The warnings presented below in this Safety Data Sheet (SDS) comply with the 2012 OSHA Hazard Communication Standard (GHS - Globally Harmonized System of Classification and Labeling). The requirements for the labeling and warnings of consumer products may differ from those required for GHS based hazard communication.

SECTION 2. HAZARDS IDENTIFICATION

Emergency Overview

Appearance	liquid
Colour	colourless, clear
Odour	mild, pleasant

GHS Classification

Respiratory sensitisation : Category 1

GHS label elements

Hazard pictograms :



Health hazard

Signal word : Danger

Hazard statements : H334 May cause allergy or asthma symptoms or breathing difficulties if inhaled.

Precautionary statements : **Prevention:**

P261 Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray.
P285 In case of inadequate ventilation wear respiratory protection.
Response:
P304 + P341 IF INHALED: If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing.
P342 + P311 If experiencing respiratory symptoms: Call a POISON CENTER/doctor.
Disposal:
P501 Dispose of contents/container in accordance with local regulation.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Hazardous components

Chemical name	CAS-No.	Concentration [%]
Sulfuric acid, mono-C10-16-alkyl esters, sodium salts	68585-47-7	>= 1 - < 3
Proprietary Enzyme	Not Available	>= 0.1 - < 1

The exact percentages of disclosed substances are withheld as trade secrets.

SECTION 4. FIRST AID MEASURES

General advice : Move out of dangerous area.
Show this safety data sheet to the doctor in attendance.
Do not leave the victim unattended.

If inhaled : If symptoms persist, call a physician.
If unconscious, place in recovery position and seek medical advice.

In case of skin contact : Wash off immediately with plenty of water for at least 15 minutes.
Remove contaminated clothing and shoes.
Wash contaminated clothing before reuse.
If skin irritation persists, call a physician.

In case of eye contact : Rinse immediately with plenty of water for at least 15 minutes.
Remove contact lenses.
Protect unharmed eye.
Keep eye wide open while rinsing.
If eye irritation persists, consult a specialist.

If swallowed : Keep respiratory tract clear.
DO NOT induce vomiting unless directed to do so by a physician or poison control center.
Never give anything by mouth to an unconscious person.

If symptoms persist, call a physician.
Take victim immediately to hospital.

Most important symptoms and effects, both acute and delayed	:	Effects are dependent on exposure (dose, concentration, contact time). Effects are immediate and delayed. Symptoms may include shortness of breath, dry cough, and irritation of the nose, eyes, lips, mouth, and throat. May cause allergy or asthma symptoms or breathing difficulties if inhaled. Review section 2 of SDS to see all potential hazards.
Notes to physician	:	Treat symptomatically. Symptoms may be delayed.

SECTION 5. FIREFIGHTING MEASURES

Suitable extinguishing media	:	Water spray jet Alcohol-resistant foam Carbon dioxide (CO2) Dry chemical
Unsuitable extinguishing media	:	High volume water jet
Specific hazards during firefighting	:	Do not allow run-off from fire fighting to enter drains or water courses.
Hazardous combustion products	:	Carbon dioxide (CO2) Carbon monoxide Smoke
Specific extinguishing methods	:	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Further information	:	Standard procedure for chemical fires.
Special protective equipment for firefighters	:	Wear self-contained breathing apparatus for firefighting if necessary.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures	:	Use personal protective equipment. Ensure adequate ventilation.
Environmental precautions	:	Prevent product from entering drains. Prevent further leakage or spillage if safe to do so. If the product contaminates rivers and lakes or drains, inform respective authorities.
Methods and materials for containment and cleaning up	:	Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Keep in suitable, closed containers for disposal.

SECTION 7. HANDLING AND STORAGE

Advice on safe handling	:	Do not breathe vapours or spray mist. Avoid exposure - obtain special instructions before use. Avoid contact with skin and eyes. For personal protection see section 8. Smoking, eating and drinking should be prohibited in the application area. Provide sufficient air exchange and/or exhaust in work rooms. Dispose of rinse water in accordance with local and national regulations. Persons susceptible to skin sensitisation problems or asthma, allergies, chronic or recurrent respiratory disease should not be employed in any process in which this mixture is being used.
Conditions for safe storage	:	Keep container tightly closed in a dry and well-ventilated place. Electrical installations / working materials must comply with the technological safety standards.
Materials to avoid	:	Oxidizing agents

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Components with workplace control parameters

Contains no substances with occupational exposure limit values.

Engineering measures : effective ventilation in all processing areas

Personal protective equipment

Respiratory protection	:	In the case of vapour formation use a respirator with an approved filter.
Hand protection		
Material	:	Protective gloves
Remarks	:	The suitability for a specific workplace should be discussed with the producers of the protective gloves.
Eye protection	:	Ensure that eyewash stations and safety showers are close to the workstation location. Tightly fitting safety goggles
Skin and body protection	:	Choose body protection according to the amount and concentration of the dangerous substance at the work place.
Hygiene measures	:	When using do not eat or drink. When using do not smoke. Wash hands before breaks and at the end of workday.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	:	liquid
Colour	:	colourless, clear
Odour	:	mild, pleasant
Odour Threshold	:	No data available
pH	:	9 - 10
Melting point/freezing point	:	No data available
Boiling point	:	100 °C
Flash point	:	No data available
Evaporation rate	:	not determined
Upper explosion limit	:	Not applicable
Lower explosion limit	:	Not applicable
Vapour pressure	:	not determined
Relative vapour density	:	No data available
Density	:	1.0 g/cm3
Solubility(ies)		
Water solubility	:	soluble
Solubility in other solvents	:	not determined
Partition coefficient: n-octanol/water	:	No data available
Auto-ignition temperature	:	not determined
Thermal decomposition	:	No data available
Viscosity		
Viscosity, kinematic	:	No data available

SECTION 10. STABILITY AND REACTIVITY

Reactivity	:	Stable
Chemical stability	:	Stable under normal conditions.
Possibility of hazardous reactions	:	No decomposition if stored and applied as directed.
Conditions to avoid	:	No data available
Incompatible materials	:	Oxidizing agents

Hazardous decomposition products	:	Carbon oxides

SECTION 11. TOXICOLOGICAL INFORMATION

Potential Health Effects

Aggravated Medical Condition	:	None known.
Symptoms of Overexposure	:	Effects are dependent on exposure (dose, concentration, contact time). Effects are immediate and delayed. Symptoms may include shortness of breath, dry cough, and irritation of the nose, eyes, lips, mouth, and throat. May cause allergy or asthma symptoms or breathing difficulties if inhaled. Review section 2 of SDS to see all potential hazards. Treat symptomatically. Symptoms may be delayed.

Carcinogenicity:

IARC	No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
ACGIH	Confirmed animal carcinogen with unknown relevance to humans 2-butoxyethanol 111-76-2
OSHA	No component of this product present at levels greater than or equal to 0.1% is on OSHA's list of regulated carcinogens.
NTP	No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

Acute toxicity

Product:

Acute oral toxicity	:	Acute toxicity estimate : > 5,000 mg/kg Method: Calculation method

Components:

Sulfuric acid, mono-C10-16-alkyl esters, sodium salts:

Acute oral toxicity	:	LD50 Oral Rat: 800 - 2,700 mg/kg
Acute dermal toxicity	:	LD50 Dermal Rabbit: >= 10,000 mg/kg

Skin corrosion/irritation

Product:

Remarks: May cause skin irritation and/or dermatitis.

Serious eye damage/eye irritation

Product:

Remarks: Contact with eyes may cause irritation.

Respiratory or skin sensitisation

No data available

Germ cell mutagenicity

No data available

Carcinogenicity

No data available

Reproductive toxicity

No data available

STOT - single exposure

No data available

STOT - repeated exposure

No data available

Aspiration toxicity

No data available

Further information

Product:

Remarks: No data available

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity

No data available

Persistence and degradability

No data available

Bioaccumulative potential

Product:

Partition coefficient: n-octanol/water	:	Remarks: No data available

Mobility in soil

No data available

Other adverse effects

No data available

Product:

Regulation	40 CFR Protection of Environment; Part 82 Protection of Stratospheric Ozone - CAA Section 602 Class I Substances
Remarks	This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

Additional ecological information : No data available

SECTION 13. DISPOSAL CONSIDERATIONS

Disposal methods

Waste from residues : Do not dispose of waste into sewer.
Do not contaminate ponds, waterways or ditches with chemical or used container.
Dispose of in accordance with local regulations.

Contaminated packaging : Empty remaining contents.
Dispose of as unused product.
Do not re-use empty containers.

SECTION 14. TRANSPORT INFORMATION

Transportation Regulation: 49 CFR (USA):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: IMDG (Vessel):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: IATA (Cargo Air):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: IATA (Passenger Air):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: TDG (Canada):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

The product as delivered to the customer conforms to packaging requirements for shipment by road under US Department of Transportation (DOT) regulations. Additional transportation classifications

noted above are for reference only, and not a certification or warranty of the suitability of the packaging for shipment under these alternative transport regulations.

SECTION 15. REGULATORY INFORMATION

TSCA list : No substances are subject to a Significant New Use Rule.

No substances are subject to TSCA 12(b) export notification requirements.

EPCRA - Emergency Planning and Community Right-to-Know Act

CERCLA Reportable Quantity

Components	CAS-No.	Component RQ (lbs)	Calculated product RQ (lbs)
sodium hydroxide	1310-73-2	1000	*

*: Calculated RQ exceeds reasonably attainable upper limit.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : Respiratory or skin sensitisation

SARA 302 : No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 : The following components are subject to reporting levels established by SARA Title III, Section 313:

2-butoxyethanol	111-76-2	0.8004 %
2-(2-butoxyethoxy)ethanol	112-34-5	0.7004 %

California Prop. 65

This product does not contain any chemicals known to State of California to cause cancer, birth defects, or any other reproductive harm.

The components of this product are reported in the following inventories:

TSCA On TSCA Inventory
DSL All components of this product are on the Canadian DSL

For information on the country notification status for other regions please contact the manufacturer's regulatory group.

Inventory Acronym and Validity Area Legend:

TSCA (USA), DSL (Canada), NDSL (Canada)

SECTION 16. OTHER INFORMATION

Further information

NFPA:

HEALTH	**2**
FLAMMABILITY	**1**
INSTABILITY	**0**
SPECIAL HAZARD.	

0 = not significant, 1 =Slight,
2 = Moderate, 3 = High
4 = Extreme

HMIS III:

HEALTH	**1***
FLAMMABILITY	**1**
PHYSICAL HAZARD	**0**

0 = not significant, 1 =Slight,
2 = Moderate, 3 = High
4 = Extreme, * = Chronic

OSHA - GHS Label Information:

Hazard pictograms :



Health hazard

Signal word : **Danger:**
Hazard statements : May cause allergy or asthma symptoms or breathing difficulties if inhaled.
Precautionary statements :

Prevention: Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray. In case of inadequate ventilation wear respiratory protection.
Response: IF INHALED: If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing. If experiencing respiratory symptoms: Call a POISON CENTER/doctor.

Disposal: Dispose of contents/container in accordance with local regulation.

Version:	2.1
Revision Date:	06/16/2020
Print Date:	08/27/2020

We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. Users should make their own investigations to determine the suitability and applicability of the information for their particular purposes. This SDS has been prepared by the Compliance Services organization supporting this manufacturer, supplier or distributor.