SAFETY DATA SHEET



1. Identification

Product identifier GP PRO ActiveAire® Urinal Screen, Coastal Breeze

Product list GP PRO ActiveAire® Low-Splash Deodorizer Urinal Screen, Coastal Breeze SKU 48260

GP PRO ActiveAire® Deodorizer Urinal Screen, Coastal Breeze SKU 48270

Other means of identification None.

Recommended use Washroom urinal care

Recommended restrictions None known.

Manufacturer/Importer/Supplier/Distributor information

Company name Georgia-Pacific Consumer Products LP

Address 133 Peachtree Street, NE

Atlanta, GA 30303

Telephone Technical Information 866.435.5647

(M)SDS Request 404.652.5119

E-mail MSDSREQ@GAPAC.com

Emergency phone number Chemtrec - Emergency 800.424.9300

2. Hazard(s) identification

Emergency overview This is a con

This is a consumer product and may contain hazardous substances, as those terms are defined in the Consumer Product Safety Act (15 U.S.C. 2051 et seq.) and Federal Hazardous Substances Act (15 U.S.C. 1261 et seq.), and it is therefore exempt from the OSHA Hazard Communication Standard (29 CFR 1910.1200) when it is used in the workplace for its intended purpose and such use results in a duration and frequency of exposure not greater than the range of exposures that could reasonably by experienced by consumers when used for the same intended purpose. Please refer directly to the product label for any first aid or warning information applicable to consumer use and required by the Federal Hazardous Substances Act. This SDS is prepared pursuant to the Hazard Communication Standard (29 CFR 1910.1200) for workplace employees.

Physical hazards Not classified.

Health hazardsSensitization, skinCategory 1Environmental hazardsHazardous to the aquatic environment,Category 3

long-term hazard

OSHA defined hazards Not classified.

Label elements



Signal word Warning

Hazard statement May cause an allergic skin reaction. Harmful to aquatic life with long lasting effects.

Precautionary statement

Prevention In case of prolonged or frequently repeated contact, wear protective gloves. Do not eat, drink or

smoke when using this product. Avoid release to the environment.

Response If on skin: Wash with plenty of water. If skin irritation or rash occurs: Get medical advice/attention.

Wash contaminated clothing before reuse. Specific treatment (see section 4 on the SDS).

Storage Store away from strong oxidizing agents.

Disposal Dispose of contents/container in accordance with local/regional/national/international regulations.

Hazard(s) not otherwise

classified (HNOC)

None known.

Supplemental information None.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
BENZYL BENZOATE		120-51-4	3 - 7
2,6-DIMETHYLOCT-7-EN-2-OL		18479-58-8	0.5 - 1.5
ETHANONE, 1-(1,2,3,4,5,6,7,8-OCTAHYDRO-2,3,8,8-TETRAMETHYL-2-NAPHTHALENYL)-		54464-57-2	0.5 - 1.5
2,6-DI-TERT-BUTYL-P-CRESOL		128-37-0	0.1 - 1
BENZENEPROPANAL, 4-(1,1-DIMETHYLETHYL)ALPHA METHYL-		80-54-6	0.1 - 1
D-LIMONENE		5989-27-5	0.1 - 1
Other components below reportable le	evels		80 - 100

Composition comments

This product is a multi-component mixture of fragrance ingredients. The specific chemical identities of the ingredients not listed herein are considered to be trade secrets by the manufacturer and are withheld in accordance with the provisions of 29 CFR 1910.1200.

4. First-aid measures

Inhalation Under normal conditions of intended use, this material is not expected to be an inhalation hazard.

Call a physician if symptoms develop or persist. Move to fresh air.

Wash with soap and water. In case of eczema or other skin disorders: Seek medical attention and Skin contact

take along these instructions.

Flush eyes immediately with large amounts of water. Get medical attention if irritation develops Eye contact

and persists.

Rinse mouth. Do not induce vomiting without advice from poison control center. If vomiting occurs, Ingestion

keep head low so that stomach content doesn't get into the lungs. Get medical attention if

May cause an allergic skin reaction. Dermatitis. Rash. Direct contact with eyes may cause

symptoms occur.

temporary irritation.

Most important

symptoms/effects, acute and

delayed

Indication of immediate medical attention and special treatment needed

Provide general supportive measures and treat symptomatically. Symptoms may be delayed. Keep

individual under observation.

Ensure that medical personnel are aware of the material(s) involved, and take precautions to **General information**

protect themselves. Show this safety data sheet to the doctor in attendance.

5. Fire-fighting measures

Suitable extinguishing media

Unsuitable extinguishing

media

Water fog. Foam. Dry chemical powder. Carbon dioxide (CO2).

Do not use water jet as an extinguisher, as this will spread the fire.

Specific hazards arising from

the chemical

During fire, gases hazardous to health may be formed.

Special protective equipment and precautions for firefighters Self-contained breathing apparatus and full protective clothing must be worn in case of fire.

Fire fighting

equipment/instructions

Use water spray to cool unopened containers.

Use standard firefighting procedures and consider the hazards of other involved materials. Specific methods

General fire hazards No unusual fire or explosion hazards noted.

6. Accidental release measures

Personal precautions. protective equipment and emergency procedures

Provide adequate ventilation and avoid contact with skin and eyes. Wear appropriate protective equipment and clothing during clean-up. Local authorities should be advised if significant spillages cannot be contained. Remove all sources of ignition.

Methods and materials for containment and cleaning up Sweep up and shovel into suitable containers for disposal. Contain the spill, then place in a suitable container. For waste disposal, see section 13 of the SDS. Prevent product from entering drains.

Avoid release to the environment. If large quantities enter a waterway, advise local authorities. **Environmental precautions**

7. Handling and storage

Precautions for safe handling Avoid contact with eyes, skin, and clothing. Provide adequate ventilation. When using, do not eat,

drink or smoke. Do not taste or swallow. Wear appropriate personal protective equipment. Avoid

release to the environment.

Conditions for safe storage, including any incompatibilities Keep containers tightly closed in a dry, cool and well-ventilated place. Store away from incompatible materials (see Section 10 of the SDS). Keep away from direct sunlight. Keep away from heat, sparks and open flame. Keep out of the reach of children. Storage 32-90°F (0-32.2°C) for less than 30 days. Optimal conditions for long term storage 60-75°F (15.5-23.8°C), Acceptable conditions for long term storage 40-80°F (4.4-26.6°C).

8. Exposure controls/personal protection

Occupational exposure limits

The following constituents are the only constituents of the product which have a PEL, TLV or other recommended exposure limit. At this time, the other constituents have no known exposure limits.

US.	ACGIH	Threshold	Limit Values
-----	--------------	-----------	---------------------

Components	Туре	Value	Form
2,6-DI-TERT-BUTYL-P-CR ESOL (CAS 128-37-0)	TWA	2 mg/m3	Inhalable fraction and vapor.
US. NIOSH: Pocket Guide to Chen	nical Hazards		
Components	Туре	Value	
2,6-DI-TERT-BUTYL-P-CR	TWA	10 mg/m3	

Biological limit values No biological exposure limits noted for the ingredient(s).

Appropriate engineering

ESOL (CAS 128-37-0)

controls

General ventilation normally adequate.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses or goggles if handling large quantities.

Skin protection

In case of prolonged or frequently repeated contact, wear appropriate gloves. **Hand protection**

Other None necessary under normal conditions of use. Wear appropriate gloves if handling large

quantities.

Respiratory protection

Under normal conditions of use respiratory protection is not expected to be required.

Thermal hazards Not applicable.

General hygiene considerations

When using, do not eat, drink or smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely

wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties

Appearance

Solid. Physical state Solid **Form** Blue Color

Odor Characteristic. **Odor threshold** Not available. pН Not available.

Melting point/freezing point 140 - 185 °F (60 - 85 °C)

Initial boiling point and boiling

range

Not available.

> 199.4 °F (> 93.0 °C) Flash point Not available.

Evaporation rate Flammability (solid, gas) Not available. Upper/lower flammability or explosive limits Flammability limit - lower

Not available.

(%)

Flammability limit - upper

(%)

Not available.

Explosive limit - lower (%)

Not available. Not available.

Explosive limit - upper (%) Vapor pressure Not available. Not available. Vapor density Relative density Not available.

Solubility(ies)

Insoluble Solubility (water) **Partition coefficient** Not available.

(n-octanol/water)

Auto-ignition temperature > 626 °F (> 330 °C) > 572 °F (> 300 °C) **Decomposition temperature Viscosity** Not available.

Other information

Explosive properties Not explosive. Oxidizing properties Not oxidizing.

10. Stability and reactivity

Reactivity The product is stable and non-reactive under normal conditions of use, storage and transport.

Chemical stability Material is stable under normal conditions.

Possibility of hazardous

reactions

No dangerous reaction known under conditions of normal use.

Conditions to avoid Avoid temperatures above 210 °C. Heat, flames and sparks. Extremes of temperature and direct

sunlight.

Strong oxidizing agents. Incompatible materials

Hazardous decomposition

products

Carbon dioxide, carbon monoxide, and unburned hydrocarbons.

11. Toxicological information

Information on likely routes of exposure

Inhalation Health injuries are not known or expected under normal use.

Skin contact May cause an allergic skin reaction.

Eye contact Direct contact with eyes may cause temporary irritation.

Not applicable under normal conditions of use. May cause gastrointestinal irritation if ingested. Ingestion

Symptoms related to the physical, chemical and toxicological characteristics May cause an allergic skin reaction. Dermatitis. Rash. Direct contact with eyes may cause temporary irritation.

Information on toxicological effects

May cause an allergic skin reaction. **Acute toxicity**

Components **Species Test Results**

2,6-DI-TERT-BUTYL-P-CRESOL (CAS 128-37-0)

Acute Dermal

LD50 Rat > 2000 mg/kg, 24 hours

Oral

LD50 Rat > 6000 mg/kg

BENZYL BENZOATE (CAS 120-51-4)

Acute **Dermal**

LD50 Rat 4000 mg/kg

Oral LD50

Rat 2000 mg/kg

Material name: GP PRO ActiveAire® Urinal Screen, Coastal Breeze

Components Species Test Results

D-LIMONENE (CAS 5989-27-5)

Acute Oral

LD50 Mouse 5600 - 6600 mg/kg

1700 mg/kg

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation Prolonged skin contact may cause temporary irritation.

Serious eye damage/eye Direct contact with eyes may cause temporary irritation.

irritation

Respiratory or skin sensitization

Respiratory sensitization Not classified.

Skin sensitization May cause an allergic skin reaction.

Germ cell mutagenicity

No data available to indicate product or any components present at greater than 0.1% are

mutagenic or genotoxic.

Carcinogenicity This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.

IARC Monographs. Overall Evaluation of Carcinogenicity

Not listed

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

US. National Toxicology Program (NTP) Report on Carcinogens

Not listed.

Reproductive toxicity Not classified.

Specific target organ toxicity - Not classified.

single exposure

Specific target organ toxicity - N

repeated exposure

Not classified.

Aspiration hazard Not applicable.

Chronic effects Not hazardous under normal conditions of use.

12. Ecological information

Ecotoxicity Harmful to aquatic life with long lasting effects.

Product Species Test Results

GP PRO ActiveAire® Urinal Screen, Coastal Breeze

Aquatic

AlgaeIC50Algae25000 mg/L, 72 Hours estimatedCrustaceaEC50Daphnia1275.6503 mg/L, 48 Hours estimated

Components Species Test Results

2,6-DI-TERT-BUTYL-P-CRESOL (CAS 128-37-0)

Aquatic

Acute

Crustacea EC50 Invertebrates (Invertebrates) 0.48 mg/l, 48 hours

BENZENEPROPANAL, 4-(1,1-DIMETHYLETHYL)-.ALPHA.-METHYL- (CAS 80-54-6)

Aquatic

Crustacea EC50 Daphnia 10.7 mg/L, 48 Hours

BENZYL BENZOATE (CAS 120-51-4)

Aquatic

Acute

Fish LC50 Fish 0.29 mg/l, 96 hours

Chronic

Crustacea NOEC Daphnia 0.25 mg/l, 21 days

Components Species Test Results

D-LIMONENE (CAS 5989-27-5)

Aquatic

Crustacea EC50 Water flea (Daphnia pulex) 69.6 mg/l, 48 hours

Fish LC50 Fathead minnow (Pimephales promelas) 0.619 - 0.796 mg/l, 96 hours

ETHANONE, 1-(1,2,3,4,5,6,7,8-OCTAHYDRO-2,3,8,8-TETRAMETHYL-2-NAPHTHALENYL)- (CAS 54464-57-2)

Aquatic

Acute

Fish LC50 Fish 1.3 mg/l, 96 hours

Persistence and degradability

No data is available on the degradability of this product.

Bioaccumulative potential

Partition coefficient n-octanol / water (log Kow)

2,6-DI-TERT-BUTYL-P-CRESOL5.1BENZYL BENZOATE3.97D-LIMONENE4.57

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation

potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructions

This product, if discarded, is not considered a hazardous waste under Federal Hazardous Waste

Regulations 40 CFR 261. If processing, use, or contamination alters the material, the waste must be tested using methods described in 40 CFR 261 to determine if it meets applicable definitions of

hazardous wastes. Do not incinerate used or unused product.

Local disposal regulations Dispose in accordance with all applicable regulations.

Hazardous waste code The waste code should be assigned in discussion between the user, the producer and the waste

disposal company.

Waste from residues / unused

products

Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see:

Disposal instructions).

Contaminated packaging Do not re-use empty containers. Empty containers should be taken to an approved waste handling

site for recycling or disposal. Since emptied containers may retain product residue, follow label

warnings even after container is emptied.

14. Transport information

DOT

Not regulated as dangerous goods.

Transport in bulk according to

Not available.

Annex II of MARPOL 73/78 and

the IBC Code

15. Regulatory information

US federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication

Standard, 29 CFR 1910,1200.

Toxic Substances Control

Act (TSCA)

All components of the mixture on the TSCA 8(b) inventory are designated "active".

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

^{*} Estimates for product may be based on additional component data not shown.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous

No (Exempt)

chemical

SARA 313 (TRI reporting)

Not regulated.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act

Not regulated.

(SDWA)

US state regulations

California Proposition 65

This product contains no listed substances known to the State of California to cause cancer, birth defects or other reproductive harm, at levels which would require a warning under the statute.

International Inventories

Country(s) or region Inventory name On inventory (yes/no)*

Canada Domestic Substances List (DSL) Yes

United States & Puerto Rico Toxic Substances Control Act (TSCA) Inventory Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date April-16-2016
Revision date August-16-2020

Version # 03

HMIS® ratings Health: 2

Flammability: 1 Physical hazard: 0

NFPA ratings Health: 2

Flammability: 1 Instability: 0

Disclaimer This SDS is intended to quickly provide useful information to the user(s) of this material or product.

It is not intended to serve as a comprehensive discussion of all possible risks or hazards, and it assumes a reasonable use of the product. The information contained in this SDS is believed to be accurate as of the date of preparation of this SDS and has been compiled from sources believed to be reliable. It is offered for your consideration, investigation and verification. The user or handler (or their employer) should consider the specific conditions in which this material will be used, handled, or stored and determine what specific safety or other precautions are required. Employers should ensure that their employees, agents, contractors, and customers who will use the product receive adequate warnings and safe handling procedures, including a current SDS. Product users or handlers (or their employer) who are unsure of what specific precautions are required should consult their employer, product supplier, or safety or health professionals before handling or working with this product. Please notify us immediately if you believe this SDS or other

safety and health information about this product is inaccurate or incomplete.

Revision information Product and Company Identification: Alternate Trade Names

Hazard(s) identification: Emergency overview

Composition / Information on Ingredients: Ingredients

Composition/information on ingredients: Component information Exposure controls/personal protection: Occupational exposure limits

Physical and chemical properties: Appearance Physical and chemical properties: Color

Physical and chemical properties: Explosive properties Physical and chemical properties: Flammability (solid, gas) Physical and chemical properties: Oxidizing properties Regulatory information: California Proposition 65

Regulatory information: Toxic Substances Control Act (TSCA)

Material name: GP PRO ActiveAire® Urinal Screen, Coastal Breeze