



LED BACKLIT PANEL



PRODUCT FEATURES

- Tunable Wattage & CCT Models Available
- Seamless White Finish Frame
- Concave-Convex Edge Fold Aluminum Backplate
- Back-lit LED Technology
- PMMA Optic Anti-Yellow
- UL / DLC Certified
- 0-10V Dimming
- High Luminous Efficiency
- Glare-free Lighting
- 50,000 Hour Lifetime Rating
- 5-Year Limited Warranty
- Operational Temperature Range -4°F to 104°F (-20°C to 40°C)

PRODUCT SPECIFICATIONS

MODEL	POWER (W)	LUMENS (LM)	CCT (K)	DIMENSIONS (FT)	EFFICIENCY (lm/W)	BEAM ANGLE
CLP99-2X2BLP-29W40K / 50K	29	3190	4000 / 5000	2 X 2	110	120°
CLP99-2X4BLP-49W40K / 50K	49	5300	4000 / 5000	2 X 4	108	120°
CLP99-2X2BLP-15/19/24/29W-30K-40K-50K TUNABLE WATTAGE & CCT	15	1950	3000	2 X 2	130	120°
	19	2470	4000			
	24	3120	5000			
	29	3770	5000			
CLP99-2X4BLP-29/34/39/49W-30K-40K-50K TUNABLE WATTAGE & CCT	29	3770	3000	2 X 4	130	120°
	34	4420	4000			
	39	5070	5000			
	49	6370	5000			

