




# WATER-COOLED PORTABLE AIR CONDITIONER

**1.3 TON, 16,000 BTU, 115V, BY GLOBAL INDUSTRIAL™**

## Keep your workspace cool with this Global Industrial™ Water-Cooled Portable Air Conditioner.

Designed for permanent or temporary spot cooling, this unit features durable metal housing and is equipped with four swivel casters, two of which are locking, for easy maneuverability. Unlike air-cooled models that utilize a fan to cool the condenser coil, this model uses water, which is quieter, more energy efficient, and eliminates the need to vent hot exhaust. This unit requires a constant supply of cold or chilled water to operate and access to a drain (janitor/utility sink, regular sink, or floor drain). Ideal for use in health care facilities, restaurants, server rooms, and other commercial spaces, this unit provides greater cooling capacity per amp of power vs. air-cooled models and is highly suitable for high ambient air temperature applications.

### KEY FEATURES

-  **ENERGY EFFICIENT**  
More energy efficient than air-cooled units, this A/C uses water to cool the condenser fan, eliminating the need to vent hot exhaust air
-  **IMPRESSIVE COOLING CAPACITY**  
Featuring a 1.3-ton cooling capacity, this unit provides spot cooling from 64 to 86°F and room cooling from 32 to 86°F
-  **SAFE OPERATION**  
Includes built-in safety features such as compressor time delay, compressor overload protection, a high/low pressure warning, an anti-freezing device, & an auto-restart function

### PRODUCT DETAILS

Number of Speeds	2
Refrigerant	R-32
BTU Cooling	16,000
Material	Galvanized Steel
Phase	1
Watts Cooling	930 W
Hertz	60 Hz
Amp Circuit	15 A
Amps Cooling	8.1 A
Operating Temperature	64 to 113°F
Voltage	115 V
Includes	Cold Air Supply Chutes & Water Hoses
Ton	1.3
Cooling System	Water
Condensate Tank	3.9 gal.
Agency Listings	ETL & cETL
Warranty	3-Year Limited


### WEIGHT & DIMENSIONS

Width	20-1/2"
Depth	26-1/2"
Height	41"
Weight	196 lbs.
Cord Length	10'
Coverage Area	410 sq. ft.



### MADE TO EXCEED.®

- ✓ Cooling for up to 410 sq. ft.
- ✓ Single-phase, 115V AC power supply
- ✓ Temperature, fan, and timer controls



Digital control panel



Water inlet and outlet with quick connect fittings



Convenient access to condensate tank



Onboard hose storage



**Also available:** Model Number 604217  
Global Industrial™ Portable Air Conditioner w/ Cold Air  
Nozzles, 7.5 Ton, 92,000 BTU, 460V