


ELECTRIC PALLET JACK

**3,300 LB. CAP., 27" X 48" FORKS
BY GLOBAL INDUSTRIAL™**






Increase productivity and reduce the risk of workplace injuries with the Global Industrial™ Electric Pallet Jack.

Constructed from heavy-duty steel with a durable powder coat finish, this unit combines safety, a long battery life, and consistent power output to quickly move large quantities of palletized goods at consistently faster speeds. Engineered with efficiency in mind, this machine moves at a max speed of 2.7 mph when loaded to help improve inventory management, stock organization, and loading/unloading trucks.

For added safety and efficiency, this pallet jack is powered by a rechargeable lithium iron phosphate (LiFePO4) battery. This compact, lightweight battery is non-toxic, non-contaminating, built to withstand extreme weather conditions, and has a longer lifecycle than other batteries. It has an excellent discharge rate and remains cool at high temperatures, allowing this jack to be used in a variety of commercial and industrial settings.

KEY FEATURES INCLUDE:

-  **BUILT FOR VERSATILITY**
Ideal for use in warehouses, manufacturing plants, distribution centers, retail stores, loading docks, & more
-  **HEAVY-DUTY PERFORMANCE**
Easily transport up to 3,300 lbs. of palletized goods throughout your warehouse or facility
-  **SUPERIOR MANEUVERABILITY**
Featuring a 57° turning radius, this jack easily maneuvers around tight corners and spaces

WEIGHT & DIMENSIONS

| | |
|------------------------|----------|
| Fork Length | 48" |
| Fork Width | 6" |
| Overall Height | 48" |
| Overall Length | 64" |
| Width | 27" |
| Distance Between Forks | 15" |
| Distance Across Forks | 27" |
| Fork Raised Height | 7-11/16" |
| Fork Lowered Height | 3" |
| Weight | 309 lbs. |

PRODUCT DETAILS

| | |
|-------------------------|-----------------------|
| Assembly Required | No |
| Material | Steel |
| Type | Self-Propelled |
| Style | Standard Forks |
| Color | Yellow |
| Battery | Lithium Iron 24V/20AH |
| Wheel Type | 2 Load, 2 Steer |
| Capacity | 3,300 lbs. |
| Duty Cycle Per Charge | 3 Hours |
| Travel Speed | 2.7 MPH |
| Certifications | cETL |
| Manufacturer's Warranty | Limited 1-Year |

HIGHLIGHTS

- ✓ Rechargeable LiFePO4 battery for three hours of continuous operation
- ✓ Override brake allows you to manually move the jack
- ✓ Includes (1) charger & (1) battery



Ergonomic Features
Reduce Fatigue



Toe Guard



Emergency Stop
Button



Durable Steel
Construction